

Unit 9, 12 Mars Rd Lane Cove NSW 2066 Australia

Tel: +61 2 9420 0690 Fax: +61 2 9420 0692 www.cap-xx.com

CAP-XX (Australia) Pty Ltd ABN 28 077 060 872 ACN 077 060 872

# HS106 / HS206 SUPERCAPACITOR Datasheet Rev 4.3, July 2018

This Datasheet should be read in conjunction with the CAP-XX Supercapacitors Product Guide which contains information common to our product lines.

### **Electrical Specifications**

The HS106 is a single cell supercapacitor. The HS206 is a dual cell supercapacitor with two HS106 cells in series, so HS206 capacitance = Capacitance of HS106/2 and HS206 ESR =  $2 \times HS106 ESR$ .

#### **Table 1: Absolute Maximum Ratings**

Parameter	Name		Conditions	Min	Typical	Max	Units
Terminal	Vpeak	HS106		0		2.9	V
Voltage		HS206				5.8	
Temperature	Tmax			-40		+85	°C

Parameter	Name		Conditions	Min	Typical	Max	Units
Terminal Voltage	Vn	HS106		0		2.75	v
		HS206		0		5.5	
Capacitance	C	HS106	DC, 23°C	1040	1300	1560	mF
		HS206		520	650	780	
ESR	ESR	HS106	DC, 23°C		30	36	mΩ
LJK		HS206			55	66	
Leakage Current	$I_L$		2.75V, 23°C 120hrs		1	2	μA
RMS Current	I <sub>RMS</sub>		23°C			6	Α
Peak Current <sup>1</sup>	IP		23°C			30	Α

#### Table 2: Electrical Characteristics

<sup>1</sup>Non-repetitive current, single pulse to discharge fully charged supercapacitor.

#### Table 3: Thickness

HS106F	1.3mm	No adhesive tape on underside of the supercapacitor	HS106G		Adhesive tape on underside, release tape removed
HS206F	2.7mm		HS206G	2.8mm	



#### **Definition of Terms**

In its simplest form, the Equivalent Series Resistance (ESR) of a capacitor is the real part of the complex impedance. In the time domain, it can be found by applying a step discharge current to a charged cell as in Fig. 1. In this figure, the supercapacitor is pre-charged and then discharged with a current pulse, I = 1A for duration 0.01 sec.




Figure 1: Effective capacitance, instantaneous capacitance and ESR for an HS206

The ESR is found by dividing the instantaneous voltage step ( $\Delta V$ ) by I. In this example = (5.492V - 5.446V)/1A = 46m $\Omega$ .

The instantaneous capacitance  $(C_i)$  can be found by taking the inverse of the derivative of the voltage, and multiplying it by I.

The effective capacitance for a pulse of duration  $\Delta t_n$ ,  $Ce(\Delta t_n)$  is found by dividing the total charge removed from the capacitor ( $\Delta Q_n$ ) by the voltage lost by the capacitor ( $\Delta V_n$ ). For constant current  $Ce(\Delta t_n) = I x$  $\Delta t_n/\Delta V_n$ . Ce increases as the pulse width increases and tends to the DC capacitance value as the pulse width becomes very long (~10 secs). After 2msecs, Fig 1 shows the voltage drop  $V_{2ms} = (5.446 \text{ V} - 5.413 \text{ V}) =$ 33mV. Therefore Ce(2ms) = 1A x 2ms/33mV = 60.6mF. After 10ms, the voltage drop = 5.446 V - 5.379 V =67mV. Therefore Ce(10ms) = 1 A x 10ms/67mV = 149mF. The DC capacitance of an HS206 = 0.65 F. Note that  $\Delta V$ , or IR drop, is not included because very little charge is removed from the capacitor during this time. Ce shows the time response of the capacitor and it is useful for predicting circuit behavior in pulsed applications.



# **Measurement of DC Capacitance**







Fig 2 shows the measurement of DC capacitance by drawing a constant 100mA current from a fully charged supercapacitor and measuring the time taken to discharge from 1.5V to 0.5V for a single cell, or from 3V to 1V for a dual cell supercapacitor. In this case,  $C = 0.1A \times 14.6s / 2V = 730mF$ , which is well within the 650mF +/- 20% tolerance for an HS206 cell.



**Measurement of ESR** 





Fig 3 shows DC measurement of ESR by applying a step load current to the supercapacitor and measuring the resulting voltage drop. CAP-XX waits for a delay of 50 $\mu$ s after the step current is applied to ensure the voltage and current have settled. In this case the ESR is measured as  $52mV/1A = 52m\Omega$ .



#### **Effective Capacitance**






Fig 4 shows the effective capacitance for the HS106, HS206 @ 23°C. This shows that for a 1ms PW, you will measure 12% of DC capacitance or 156mF for an HS106 or 78mF for an HS206. At 10ms you will measure 27% of the DC capacitance, and at 100ms you will measure 63% of DC capacitance. Ceffective is a time domain representation of the supercapacitor's frequency response. If, for example, you were calculating the voltage drop if the supercapacitor was supporting 1A for 10ms, then you would use the Ceff(10ms) = 27% of DC capacitance = 176mF for an HS206, so Vdrop = 1A x ESR + 1A x duration/C = 1A x 55m $\Omega$  + 1A x 10ms / 176mF = 112mV. The next section on pulse response shows how the effective capacitance is sufficient for even short pulse widths.

#### **Pulse Response**





Fig 5 shows that the HS206 supercapacitor does an excellent job supporting a GPRS class 10 pulse train, drawing 1.8A for 1.1ms at 25% duty cycle. The source is current limited to 0.6A and the supercapacitor provides the 1.2A difference to achieve the peak current. At first glance the freq response of Fig 8 indicates the supercapacacitor would not support a 1ms pulse, but the Ceff of 65mF coupled with the low ESR supports this pulse train with only ~80mV droop in the supply rail.

Fig 5: HS206 Pulse Response with GPRS Class 10 Pulse Train





### **DC** Capacitance variation with temperature





Fig 6 shows that DC capacitance is approximately constant with temperature.




### ESR variation with temperature

Figure 7: ESR change with temperature

Fig 7 shows that ESR at -40°C is ~2.5 x ESR at room temp, and that ESR at 70°C is ~0.8 x ESR at room temperature.




# **Frequency Response**



#### HS206 Magnitude and Phase vs. Frequency

Fig 8: Frequency Response of Impedance (biased at 5.5V with a 50mV test signal)



HS206 ESR, Capacitance and Inductance vs. Frequency

Fig 9: Frequency Response of ESR, Capacitance & Inductance

Fig 8 shows the supercapacitor behaves as an ideal capacitor until approx 2.5 Hz when the magnitude no longer rolls off proportionally to 1/freq and the phase crosses -45°. Performance of supercapacitors with frequency is complex and the best predictor of performance is Fig 4 showing effective capacitance as a function of pulsewidth.



#### Leakage Current




Fig 10: Leakage Current

Fig 10 shows the leakage current for HS106 at room temperature. The leakage current decays over time, and the equilibrium value leakage current will be reached after ~120hrs at room temperature. The typical equilibrium leakage current is  $1.5\mu$ A at room temperature. At 70°C leakage current will be ~10 $\mu$ A.




Fig 11: Charging an HS106 with low current

The corollary to the slow decay in leakage currents shown in Fig 10 is that charging a supercapacitor at very low currents takes longer than theory predicts. At higher charge currents, the charge rate is as theory predicts. For example, it should take 1.3 F x 2.7V / 0.00002A = 43.3hrs to charge a 1.3 F supercapacitor to 2.7V at  $20\mu$ A, but Fig 11 shows it took 75hrs. At  $200\mu$ A charging occurs at a rate close to the theoretical rate.



#### **RMS** Current




Fig 12: Temperature rise in HS206 with RMS current

Continuous current flow into/out of the supercap will cause self heating, which limits the maximum continuous current the supercapacitor can handle. This is measured by a current square wave with 50% duty cycle, charging the supercapacitor to rated voltage at a constant current, then discharging the supercapacitor to half rated voltage at the same constant current value. For a square wave with 50% duty cycle, the RMS current is the same as the current amplitude. Fig 12 shows the increase in temperature as a function of RMS current. From this, the maximum RMS current in an application can be calculated, for example, if the ambient temperature is 40°C, and the maximum desired temperature for the supercapacitor is 70°C, then the maximum RMS current should be limited to 4.3A, which causes a 30°C temperature increase.

## **CAP-XX Supercapacitors Product Guide**

Refer to the package drawings in the CAP-XX Supercapacitors Product Guide for detailed information of the product's dimensions, PCB landing placements, active areas and electrical connections.

Refer to the CAP-XX Supercapacitors Product Guide for information on endurance and shelf life, transportation and storage, assembly and soldering, safety and RoHS/EREACH certification.